

Interscale 19" Rack Mount Chassis, Perforated

电力公用事业



Flexible 19" Chassis with integrated EMC protection and perforated side. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

认证



功能

Modular desktop case consisting of 4 assembled parts, with perforated sides

Developed according to IEC 60297-3-109 (under progress at IEC)

集成 EMC 屏蔽

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

技术参数

Table 1/2

物料号	机架高度	深度	包装数量	可用宽度	安装	符合
14826-105	1 U	221 mm	1	444 mm	机架	IEC 60297-3-100
14826-107	1 U	310 mm	1	444 mm	机架	IEC 60297-3-100
14826-205	2 U	221 mm	1	444 mm	机架	IEC 60297-3-100
14826-207	2 U	310 mm	1	444 mm	机架	IEC 60297-3-100
14826-305	3 U	221 mm	1	444 mm	机架	IEC 60297-3-100
14826-307	3 U	310 mm	1	444 mm	机架	IEC 60297-3-100

Table 2/2

物料号	EMC 屏蔽	产品系列	产品类型	类型
14826-105	是	Interscale	小尺寸机箱	通风孔
14826-107	是	Interscale	小尺寸机箱	通风孔
14826-205	是	Interscale	小尺寸机箱	通风孔
14826-207	是	Interscale	小尺寸机箱	通风孔
14826-305	是	Interscale	小尺寸机箱	通风孔
14826-307	是	Interscale	小尺寸机箱	通风孔

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE