


Novastar Raised Top Cover

Power Utilities



Raised top cover for better ventilation and heat escape.

Novastar raised top cover is robust and not dismountable from the outside.

认证



功能

Raised Top cover (31 mm) with all-round air gap of 10 mm

Top cover attached from the inside (no screws on the outside)

Suitable for placing heavy parts on the top cover

Incl. grounding

Robust version, load-carrying capacity 50 kg

技术参数

Table 1/1

物料号	深度	颜色	颜色代码	产品类型	类型	宽度
25230-039	500 mm	暗灰色	RAL 7021	机柜/机架顶盖	升高	553 mm

物料号	深度	颜色	颜色代码	产品类型	类型	宽度
25230-142	1000 mm	暗灰色	RAL 7021	机柜/机架顶盖	升高	553 mm
25230-037	800 mm	暗灰色	RAL 7021	机柜/机架顶盖	升高	553 mm
25230-141	900 mm	暗灰色	RAL 7021	机柜/机架顶盖	升高	553 mm
25230-038	600 mm	暗灰色	RAL 7021	机柜/机架顶盖	升高	553 mm

其他产品详情

Please order lifting eye separately if required.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE