

RackPower Basic PDU, RB0xxx, 230/400 VAC, 3-phase

电力公用事业

模块化、紧凑型 PDU。Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 / C19 Combo outlets.

功能

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

1RU 铝制型材

可调节的免工具安装

技术参数

Table 1/2

物料号	产品类型	插座类型	颜色	长度	交流电压	深度
RB0450	插排	IEC C13, IEC C13/C19	黑色	1490 mm	230 V	55 mm
RB0850	插排	IEC C13, IEC C13/C19	黑色	1780 mm	230 V	55 mm

Table 2/2

物料号	宽度
RB0450	56 mm

物料号	宽度
RB0850	56 mm

ADDITIONAL PRODUCT DETAILS

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE