

Varistar CP Double Steel Door, Perforated, 3-Point Locking

电力公用事业

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

功能

Double perforated steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

标准安装，右门上有锁

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

技术参数

Table 1/2						
物料号	机架高度	高度	宽度	颜色	色号	符合
21630-020	42 U	2000 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-021	47 U	2200 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-022	52 U	2450 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-027	42 U	2000 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-028	47 U	2200 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3

物料号	机架高度	高度	宽度	颜色	色号	符合
21630-029	52 U	2450 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-448	24 U	1200 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-449	24 U	1200 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-450	29 U	1400 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-451	29 U	1400 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-452	33 U	1600 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-453	33 U	1600 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-454	38 U	1800 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-455	38 U	1800 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2					
物料号	锁定类型	产品类型	防护等级	类型	搭配使用
21630-020	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-021	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-022	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-027	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-028	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-029	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP

物料号	锁定类型	产品类型	防护等级	类型	搭配使用
21630-448	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-449	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-450	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-451	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-452	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-453	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-454	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP
21630-455	3-Point Locking	机柜门	IP20	Steel Double Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE