

Varistar CP Steel Door, Perforated With 3-Point Locking

电力公用事业

适用于 IP 20 应用的 Varistar CP 开孔钢制门，3 点锁定。

功能

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

技术参数

Table 1/2

物料号	机架高度	高度	宽度	颜色	色号	符合
21630-098	42 U	2000 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-099	47 U	2200 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-100	52 U	2450 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-101	42 U	2000 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-102	47 U	2200 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-103	52 U	2450 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3

物料号	机架高度	高度	宽度	颜色	色号	符合
21630-424	24 U	1200 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-425	24 U	1200 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-426	29 U	1400 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-427	29 U	1400 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-428	33 U	1600 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-429	33 U	1600 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-430	38 U	1800 mm	600 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3
21630-431	38 U	1800 mm	800 mm	暗灰色	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2					
物料号	锁定类型	产品类型	防护等级	类型	搭配使用
21630-098	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-099	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-100	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-101	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-102	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-103	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-424	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP

物料号	锁定类型	产品类型	防护等级	类型	搭配使用
21630-425	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-426	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-427	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-428	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-429	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-430	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP
21630-431	3-Point Locking	机柜门	IP20	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE