

ACS-30 Sensing and Monitoring Module



The nVent RAYCHEM ACS-30-EU-ELEXANT650C-SMDI-MOD Module for the ACS-30 system provides smart sensor input for surface snow melting and roof & gutter de-icing applications. The Remote Monitoring Module (RMM) is used to collect sensor/temperature inputs for monitoring of the heat tracing circuits of an ACS-30 control system.

功能

The output from the ACS-30-EU-ELEXANT650C-SMDI-MOD module enables the switching of the heating circuits within the power & control module (PCM)

The ACS-30-EU-ELEXANT650C-SMDI-MOD module provides ground or roof & gutter temperature and moisture sensing for the ACS-30 control system

Ground temperature and moisture sensor (E650C-G) and roof & gutter temperature and moisture sensor (E650C-R) are sold separately

The RMM provides up to 8 sensor inputs per module with feedback to the ACS-30-EU-UIT3 interface

A single twisted pair RS-485 cable connects up to 247 RMM units providing additional temperature monitoring sensor inputs

The RMM is remotely located adjacent to the desired measurement locations

The RMM comes in 2 versions: ACS-30-EU-RMM3 (230 V) and ACS-30-EU-RMM3-24VDC (24 V), both pre-installed inside a compact enclosure

技术参数

Table 1/2

物料号	项目名称	深度	高度	外壳材料	IP 等级	安装
2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	132 mm	262 mm	聚碳酸酯	IP20	Wall Mounted

Table 2/2

物料号	项目名称	宽度
2000003973	ACS-30-EU-ELEXANT650C-SMDI-MOD	332 mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

亚太地区

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

拉丁美洲

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT