

Multiple-Entry Power/Tee Connection with Polymer Junction Box



nVent RAYCHEM JBM-100 is a modular junction box used to connect power to up to three nVent RAYCHEM BTV, QTVR, XTVR, HTV or VPL industrial parallel heating cables and integrates the functions of both connection kits and insulation entries. Offered in three versions, customized for local installation practices, each are also available with a power indicator. JBM-100-E, JBM-100-L-E; JBM-100-EP, JBM-100-L-EP; JBM-100-A, JBM-100-L-A.

功能

Simple and fast to install, spacious boxes with front access, captive lid screws and robust spring type terminals for secure fixing

Part of a modular component system, providing maximum flexibility

One range for all nVent RAYCHEM industrial parallel heating cables

Simplified design in hazardous area, integral part of system approval

Cold-applied: core sealing boot with non-curing sealant; no heat gun, no hot work permit needed

Reliable during long life: 10 year extended product warranty available, maintenance free

技术参数

防爆区气体:	1, 2
入口数量:	2
连接夹数量:	6
最大导体横截面积:	10 mm ²
防爆区粉尘:	21, 22
连接类型:	冷敷
材料:	玻璃纤维增强型聚合物
区域分类:	无危险; 危险
IP 等级:	IP66

包含穿孔: 否

安装: 在管道上

盖板附件: 螺钉固定

无卤素: 是

Table 1/2						
物料号	项目名称	环境温度	电缆入口	高度	宽度	深度
656081-000	JBM-100-L-A	-40 to 40 °C	3/4"	240 mm	220 mm	90 mm
986415-000	JBM-100-EP	-55 to 56 °C	M25	240 mm	220 mm	90 mm
300273-000	JBM-100-L-EP	-40 to 40 °C	M25	240 mm	220 mm	90 mm
831519-000	JBM-100-E	-55 to 56 °C	M25	240 mm	220 mm	90 mm
179935-000	JBM-100-A	-40 to 56 °C	3/4"	240 mm	220 mm	90 mm
395855-000	JBM-100-L-E	-40 to 40 °C	M25	240 mm	220 mm	90 mm

Table 2/2					
物料号	项目名称	包含指示灯	包含接地板	模块化	绝缘层下方
656081-000	JBM-100-L-A	是	否	否	否
986415-000	JBM-100-EP	否	是	否	否
300273-000	JBM-100-L-EP	是	是	否	否
831519-000	JBM-100-E	否	否	否	否
179935-000	JBM-100-A	否	否	否	否
395855-000	JBM-100-L-E	是	否	否	否

其他产品详情

Localized versions may exist with limited approvals and different part numbers. Contact your local sales representative.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe, Middle East, Africa	Asia Pacific	Latin America
Tel +1.800.545.6258		Tel +86.21.2412.1688	Tel +1.713.868.4800
Fax +1.800.527.5703	Tel +32.16.213.511	Fax +86.21.5426.3167	Fax +1.713.868.2333
thermal.info@nvent.com	Fax +32.16.213.604	cn.thermal.info@nvent.com	thermal.info@nvent.com
	thermal.info@nvent.com	m	

我们强大的品牌组合:

RAYCHEM PYROTENAX TRACER NUHEAT