

19" 风扇单元, 1 U, 前面板带开关

交流设备上的前装式发光电源开关，带额外的后部电源插座；适用于电源输入和电源输出电缆的机械应力消除装置。



认证



功能

可根据插箱规格进行调整

符合 DIN EN ISO 13857 标准的接触保护

技术参数

Table 1/1

物料号	交流输入电压	直流输入电压	包装数量	完成	材料	快速发货
10713-108	230V min		1	镀锌铝, 阳极氧化	钢, 铝	No
10713-112	230V		1	镀锌铝, 阳极氧化	钢, 铝	No
10713-114	115V		1	镀锌铝, 阳极氧化	钢, 铝	No
10713-111		24V min	1	镀锌铝, 阳极氧化	钢, 铝	No

物料号	交流输入电压	直流输入电压	包装数量	完成	材料	快速发货
10713-115		24V min	1	镀锌铝, 阳极氧化	钢, 铝	No
10713-110	115V		1	镀锌铝, 阳极氧化	钢, 铝	No

其他产品详情

请单独订购电源线。

可应要求提供广泛的输入电压范围 (86 ... 264 VAC)。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE