

19" 配电设备, 3 相

19" 配电箱，带 3 相输入和断路器。该装置可为设备或单相 PDU 提供 IEC C19 插座。



认证



功能

3 相配电单元用于连接单相电器件或插座

输入 3 相 400 VAC

通过 IEC 60320-C19 插座输出

每路输出都有过流保护

技术参数

深度: 250mm

产品类型: 配电设备

Table 1/1

物料号	包装数量	完成	高度	长度	材料	快速发货
60110-365	1	阳极氧化	131mm	484mm	铝, 聚酰胺	No

物料号	包装数量	完成	高度	长度	材料	快速发货
60110-366	1	阳极氧化	131mm	484mm	铝, 聚酰胺	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE