

19" 送风扇, 2 U, 切向

带切向强压送风风扇的风扇托盘。



认证



功能

2 型版本：- LE1：19" 螺栓尺寸, 风扇单元比 19" - LE2 宽：19" 宽度缩小, 便于装配

高气流

集成过滤网

技术参数

Table 1/1

物料号	交流输入电压	包装数量	材料	快速发货
60713-001	230V	1	聚酰胺 66, 聚丙烯	No
60713-004	115V	1	聚酰胺 66, 聚丙烯	No
60713-003	115V	1	聚酰胺 66, 聚丙烯	No

物料号	交流输入电压	包装数量	材料	快速发货
60713-002	230V	1	聚酰胺 66, 聚丙烯	No

其他产品详情

应要求提供 24 VDC 版本。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE