


加固型组件的装配零件



带放松脱螺纹油的装配零件，适用于加固型侧面板、水平横梁、盖板、后角。

认证



功能

用于下列固定件的螺钉：加固型侧板 - 水平横梁, 加固型侧板 - 盖板, 加固型侧板 - 后角轨

技术参数

产品类型： 装配组件

产品系列： EuropacPRO

Table 1/2

物料号	类型	长度	包装数量	螺纹尺寸	完成	材料
24566-105	沉头螺钉	7mm	100	M4		不锈钢
24560-140	方螺母		100		镀锌	钢
24566-106	沉头螺钉	10mm	100	M4		不锈钢
24566-101	沉头螺钉	14mm	100	M4		不锈钢

物料号	类型	长度	包装数量	螺纹尺寸	完成	材料
24566-100	沉头螺钉	18mm	100	M4		不锈钢
24566-104	盘头螺钉	8mm	100	M4		不锈钢
24566-103	盘头螺钉	10mm	100	M4		不锈钢
24566-102	盘头螺钉	14mm	100	M4		不锈钢

Table 2/2		
物料号	搭配	快速发货
24566-105	插箱	No
24560-140	插箱	No
24566-106	插箱	No
24566-101	插箱	No
24566-100	插箱	No
24566-104	插箱	No
24566-103	插箱	No
24566-102	插箱	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE