

带操纵杆的连接夹钳

适用于配电箱的配电夹钳。



功能

带操纵杆的连接夹钳

适用于所有导体类型

3 或 5 个导体

最大 4.00 mm²

技术参数

Table 1/3

物料号	产品类型	颜色	环境温度	夹数量	深度	高度
20118-902	固定夹	透明, 绿色	85°C max	3	18.8mm	8.4mm
20118-903	固定夹	透明, 绿色	85°C max	5	18.8mm	8.4mm

Table 2/3

物料号	材料	最大电流	最大电压	包装数量	重量	宽度
20118-902	聚碳酸酯	20A	600V	10	2.5g	18.8mm
20118-903	聚碳酸酯	20A	600V	10	4g	30mm

Table 3/3	
物料号	快速发货
20118-902	No
20118-903	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE