

CPCI 辅助背板

在桥接器后使用的辅助 CompactPCI 背板。



认证



功能

符合：PICMG 2.0 R3.0 CompactPCI 核心技术规范, PICMG 2.1 R2.0 热插拔技术参数, PICMG 2.9 R1.0 系统管理总线技术规范, PICMG 2.10 R1.0 编码键技术规范

在桥接器后使用的辅助背板

辅助背板也可用作三级背板；地址更改请参阅用户手册

技术参数

Table 1/3

物料号	产品类型	插槽数	机架高度	背板类型	系统插槽	槽宽
23006-824	背板	4	3U	CompactPCI, 32 位, 辅助	右	4HP
23006-827	背板	7	3U	CompactPCI, 32 位, 辅助	右	4HP

Table 2/3						
物料号	电压 I/O	连接器类型	电源连接器类型	多功能连接器类型	宽度	包装数量
23006-824	5V	HM 2.0	用于 M4 电缆连接片的电 源插头	SMCQ, 12 针	80mm	1
23006-827	5V	HM 2.0	用于 M4 电缆连接片的电 源插头	SMCQ, 12 针	141mm	1

Table 3/3	
物料号	快速发货
23006-824	No
23006-827	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations +1.763.422.2661 Chat with us: nvent.com/schroff	Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff	Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff	Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE