

Varistar CP EMC 机柜，IP 20，带风扇顶盖，42 U 2000H 600W 800D

物料号

10630-045



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

功能

屏蔽能力：1 GHz，60 dB，3 GHz，40 dB（经测试符合 IEC 61587 - 3 标准）

18 GHz 时屏蔽 30 dB，（经测试符合 EN 61000-5-7 标准），带符合 EN45545 标准的垫片

防护类型 IP 20

静态承载能力：1600 千克

含 4 点锁的机柜门和螺钉固定的侧板

侧面板和后面板可由一人安装

产品属性

产品类型: 机柜

产品系列: Varistar CP

框架材料: 钢

框架颜色: 暗灰色

框架颜色代码: RAL 7021

覆层材料: 钢

覆层颜色: 暗灰色

覆层颜色代码: RAL 7021
机架高度: 42U
高度: 2000mm
宽度: 600mm
深度: 800mm
静态负载: 1600kg
防护等级: IP20
符合: IEC 61587-1; IEC 60297-3-100; IEC 61587-3
完成: 粉末涂层
材料: 钢
包装数量: 1

其他产品详情

ServicePlus EMC 上提供了更多尺寸和版本。请单独订购基座/底座。如装配托盘和滑轨，需要另外订购一对角轨。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE