

# Varistar CP 抗震机柜, bellcore zone 4, EMC, 2100H 600W 600D

## 物料号

**10630-050**



## 功能

抗震安全等级高达 Bellcore Zone 4, 已根据 Telcordia GR-63 Core 使用 250 千克进行测试

静态承载能力 1600 千克

防护类型 IP55

已根据 IEC 61587 - 3 进行高屏蔽能力测试, 带 EN45545-2 防火安全垫片

## 产品属性

产品类型: 机柜

产品系列: Varistar CP

框架材料: 钢

机架高度: 42U

高度: 2000mm

宽度: 600mm

深度: 600mm

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| 静态负载: 1600kg                                                                                                    |
| 防护等级: IP55                                                                                                      |
| 符合: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63 |
| 核心区域 4                                                                                                          |
| 颜色: 暗灰色                                                                                                         |
| 颜色代码: RAL 7021                                                                                                  |
| 完成: 粉末涂层                                                                                                        |
| 频率: 50 Hz                                                                                                       |
| 材料: 钢                                                                                                           |
| Net Weight: 157.636kg                                                                                           |
| 包装数量: 1                                                                                                         |
| 耐冲击和振动性: 5g (force)                                                                                             |
| 搭配: Varistar CP                                                                                                 |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE