

卫士系列管理网关

物料号

11079-000



nVent SCHROFF Guardian 系列管理网关

是环境监控平台，旨在感知、追踪、存储和警报 IT 数据中心基础设施中的健康和​​安全参数。

平台的核心是一个紧凑的控制单元，该控制单元的高度/深度为 1 U，宽度为 250 mm，它既可以作为 19" 单元安装，也安装到数据中心机架中的任何可用空间中。

管理网关提供三个传感器管理端口，每个端口都能够监控多达 16 个传感器设备，每个端口总电缆长度为 40 米，允许单个管理网关单元监控多个机架或完整的机架通道。

除了监控温度、湿度、烟雾、门状态或水侵入等物理参数，管理网关还可以监控 nVent SCHROFF RackChiller 和行间冷却器，并且即插即用，安装便捷。

设置具有安全功能的管理网关、传感器配置、用户管理、报警和日志管理，可以通过内置的 Web 界面轻松完成。

管理网关的主要访问途径是 1 GBE 网络接口，支持 SNMP、SMTP、HTTPS、Bacnet、Modbus/TCP 和 HPI 等行业标准协议。

认证



功能

数据中心环境监控平台

紧凑的设计适合数据中心机架中的任何位置

用于设置、监控和完成设备维护的 Web 浏览器 GUI

三个连接外部传感器和 Modbus 设备的管理端口

每个管理端口可连接最多 16 个传感器或设备，总电缆长度达 40 米

自动翻页 LCD 触控显示屏

支持行业标准网络协议（HTTPS、SNMP、SMTP、Bacnet、Modbus/TCP 和 HPI）

产品属性

产品类型: 管理单元

类型: 底座装置管理网关

机架高度: 1U

高度: 45mm

宽度: 250mm

深度: 45mm

直流输入电压: 12V min

环境温度: 5 – 60°C

材料: 铝

完成: 粉末涂层

相对湿度: 5% 至 90%，无冷凝

显示屏: LCD

Net Weight: 0.275kg

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE