

适用于 CompactPCI Serial 的 PSU 19 英寸 AC/DC, 3 U, 8 HP, 312 W

物料号

13100-147



Pluggable 19" Power Supply, for CompactPCI applications. The Power Supply has a wide range AC input, a 12V DC Payload and +5 V DC Standby output.

功能

适用于 CompactPCI Serial 应用的 19" 可插拔电源模块

主动功率因数校正和主动均流功能

N+1 冗余, 热插拔

输出信号: 电流存在信号, 电源故障, PS_ON 和 Enable

I2C 接口

高效率, > 90% at 220 VAC

产品属性

产品类型: 电源

类型: 19" 开关模式

搭配: CompactPCI 系统

交流输入电压: 90 – 264V

电源: 312W

输出电压数: 2

电压 1: 12V

电流 1: 25A
电压 2: 5V
电流 2: 2.5A
机架高度: 3U
Gross Weight: 0.948kg
包装数量: 1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE