

PXI Express 系统，4 U，8 个插槽，Gen2/3

物料号

14579-033



The nVent SCHROFF PXIe 8 Slots System has a 16HP System Slot with 4 Link configuration. 3 of the Hybrid Peripheral Slots are connected by PCIe Gen 3 links with x4 Lanes. The remaining 4 Hybrid Peripheral Slots are connected with PCIe Gen 2 links with 1 lane each.

认证



功能

PXI Express 桌面机箱, 4 U, 44 HP

1 个 PXIe 系统插槽和 7 个混合插槽

四链路系统插槽, 带 PCIe Gen3 x4 的 3 个外设槽和带 PCIe Gen2 x1 链路的 4 个外设槽

强大的散热能力, 风扇噪声低, 支持单插槽 50 W 散热 (假定出风口有 15K 温升)

温控风扇使空气从底部流向背面; 集成式机箱监测模块 (CMM)

宽幅交流输入, 电源开关位于机箱后侧, 电源按钮位于机箱正面 (顶部)

后面板含外部 10 MHz 时钟输入/输出

产品属性

产品类型: 系统
插槽数: 8
类型: 桌面式
背板类型: PXI Express, 4 链路配置
数据传输: PCIe Gen2; PCIe Gen3
每插槽的功率: 50W
交流输入电压: 100 – 240V
气流方向: 从下到后
机架高度: 4U
电源类型: 开放式框架
包含电源: 是
后部 I/O: 否
符合: PXISA PXI-5 R1.1
深度: 315mm
Gross Weight: 15kg
包装数量: 1

其他产品详情

系统符合 IEC 60297 - 3 - -101、 - -102、 - -103 标准以及 IEEE 1101.1、1101.10/11 标准；背板，符合 PICMG rev 3.0 和 PXI-5 标准。

可应要求提供定制系统。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE