

PXI Express 系统，4 U，18 个插槽，Gen2

物料号

14579-043



Desktop PXI Express Chassis for one PXI Express System Controller with up to 16 HP and 7 PXI or PXI Express Boards with 4 HP Width.

认证



功能

PXI Express 桌面机箱, 4 U, 84 HP, 带把手和 19 英寸安装支架

1 个 16 HP 宽的 PXI Express 系统插槽, 1 个 PXI Express 定时插槽和 16 个混合插槽

强大的散热能力, 风扇噪声低, 支持单插槽 50 W 散热 (假定出风口有 15K 温升)

温控风扇使空气从底部流向背面; 集成式机箱监测模块 (CMM)

宽幅交流输入, 电源开关位于机箱后侧, 前面板 (顶部) 的电源按钮 后面板外部 10 MHz 时钟输入/输出

Gen 2 PCIe switching with a four-link (4x1) System Slot

产品属性

产品类型: 系统

插槽数: 18

类型: 桌面式

背板类型: PXI Express, 4 链路配置
数据传输: PCIe Gen2
每插槽的功率: 50W
交流输入电压: 100 – 240V
气流方向: 从下到后
机架高度: 4U
电源类型: 开放式框架
包含电源: 是
后部 I/O: 否
符合: PXISA PXI-5 R1.1
深度: 355mm
包装数量: 1
PXI Express 定时插槽数量: 1

其他产品详情

系统符合 IEC 60297-3-101、-102、-103 标准以及 IEEE 1101.1、1101.10/11 标准；背板，符合 PICMG 修订版 3.0 和 PXI-5 标准

可应要求提供定制系统

警告

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE