


重型通用伸缩滑轨，2 U 300L

物料号

20110-190



伸缩滑轨，承载能力 10 至 100 kg，延长长度 > 100%，19" 版本带横向安装功能。坚固耐用的伸缩滑轨 - 适合安装 19 英寸机箱，适合安装来自我们的产品组合的服务器机箱。由于结构极其稳固，而且承载能力很高，伸缩滑轨也可以与特别重的机箱一起使用。



功能

静态承载能力每对 72 - 100 千克
在 19" 支柱上横向安装（不占用 19" 平面即可安装延长部件/抽屉）
终点挡板控制
延长长度 > 100%
轨道宽度 k = 19.1 mm, 延长部件/抽屉最大安装宽度 w = 411 mm

产品属性

长度: 300mm
包装数量: 2
完成: 镀锌
材料: 钢
产品类型: 伸缩滑轨
静态负载: 77kg
类型: 通用型
Net Weight: 1.3kg

其他产品详情

要在 19" 面板上安装，请单独订购装配套件。

在非标准应用中，无需附加组件也可安装通用伸缩滑轨，除 19" 机柜外也是如此。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE