

适于 Guardian Management Gateway 的数字触点传感器（输入），带 12V 电源

物料号

21070-125



用于监测数字输入的外部传感器，带 2 个 RJ45 连接器。最多可以通过跳线串联 16 个传感器，并将这些传感器连接至一个 Guardian Management 端口。

功能

适用于 Guardian Management Gateway 的外部传感器

一个端口最多可监测 16 个传感器设备，总电缆长度为 40 米

nVent SCHROFF Guardian 传感器连接后，网页界面将显示它的类型和序列号

金属机箱

易于安装

2 x RJ 45 连接

可轻松通过 CAT6 跳线（或屏蔽性更高的电缆）串联

产品属性

产品类型: 传感器

类型: 数字触点

搭配: Guardian Management Gateway

Gross Weight: 0.097kg

包装数量: 1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE