


接地锁紧螺母 M6，100 个

物料号

21120-132



锁紧螺母支持选择多种规格的螺母和螺栓尺寸，而且便于更换，不同于预先加工螺纹的孔。锁紧螺母可用在因为太薄或太软而无法加工螺纹的材料上。

认证



功能

适用装配 M4 或 M5 螺纹规格的零件

如需标准接地，请至少在一个连接点处使用接地螺母和垫圈

产品属性

完成: 镀锌

包装数量: 100

螺纹尺寸: M6

材料: 钢

产品系列: RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Comptec; Inpac; MultipacPRO

产品类型: 螺母

类型: 锁紧螺母; 接地

搭配: 前面板; Euro rack; Novastar; Varistar; Varistar CP

Net Weight: 0.49kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE