


Eurorack 19" 面板/滑轨安装, 38U, 铝锌合金

物料号

22117-356



滑动安装增量可调

认证



功能

适用于深度可调节安装

碳钢, 1.5 mm, 带 EIA 开孔

对于第三个 19" 平面上的安装, 需要 1 对 19" 面板/滑轨安装件和 2 对深度支撑

产品属性

机架高度: 38U
材料: 钢
完成: 镀锌铝
包装数量: 2
高度: 1798mm
产品系列: Eurorack
产品类型: 滑动安装座
类型: 19" 面板滑轨安装件
Net Weight: 4.25kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE