

# AirBender,卡片导向嵌件,70% 阻塞率,4HP,160mm,10个

#### 物料号

### 24563-040



nVent SCHROFF AirBender

嵌件通过在混合阻抗环境中平衡气流,可使每个插槽的散热效率提 高达

85%。它易于安装,可降低风扇噪音,同时提高整体系统性能。

#### 功能

AirBender卡片导向嵌件通过平衡混合空气阻抗环境中的气流,可使每个4HP插槽的电子系统散热效率提高达85%

70% 阻塞率: AirBender

可在关键组件较少的插槽中引入额外的空气阻抗,将气流重定向到散热关键区域,并确保所有卡片都获得更佳的散热效果

安装简单:只需将 AirBender 夹在 nVent SCHROFF 塑料卡片导向装置中,然后选择性地用螺钉将其固定

通过将风扇保持在高效运行点,有利于减少风扇产生的噪音

Air bender and CassettePRO cannot be used together in the same slot.

#### 产品属性

产品类型: 空气挡板

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac

搭配:插箱;仪器箱;系统

机架宽度: 4HP

深度: 160mm

材料: 聚碳酸酯

包装数量: 10

符合: EN 45545-2; UL® 94V-0

#### 其他产品详情

可根据要求提供具有不同阻塞率的 AirBender。

#### 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书,或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告,可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

#### **North America**

All locations +1.763.422.2661 Chat with us:

nvent.com/schroff

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

#### Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

## Middle East & India Dubai, United Arab

Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE