



# Guide Rail With Coding for CompactPCI/ VME64x, PC, 280 mm, 2.5 mm Groove Width, 多段复合式, Grey/Silver, 10个

物料号

**24568-341**



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

认证



## 功能

|                                                        |
|--------------------------------------------------------|
| 新一代编码型塑料导轨，实现 PCB 或模件盒的可靠固定                            |
| 稳定性显著提高, 得益于优化设计和高质量材料 (PC)                            |
| 提高防火安全性能, 符合 EN 45545-2 规范 R22, R23 和 R24 中的最高危险等级 HL3 |
| “无卤素” , 符合 IEC 61249-2-21 标准                           |
| 导轨可以卡入水平横梁（铝挤压件）或 1.5 mm 厚板中                           |
| 可以通过螺栓固定到 H 型和 R 型水平横梁，以满足更高的抗冲击和振动要求                  |
| 可选 ESD 夹，用于 PCB 和水平横梁之间的导电触点                           |
| 存储温度：从 -40 °C.. 130 °C                                 |

## 产品属性

|                                                                                          |
|------------------------------------------------------------------------------------------|
| 材料: 纤维增强型塑料; 铝                                                                           |
| 颜色: 灰色; 银色                                                                               |
| 包装数量: 10                                                                                 |
| 板深度: 280mm                                                                               |
| 槽宽: 2.5                                                                                  |
| 符合: EN 45545-2                                                                           |
| 完成: 阳极氧化                                                                                 |
| 产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac |
| 产品类型: 导轨                                                                                 |
| 类型: 编码                                                                                   |
| 搭配: 插箱; 仪器箱; 19" 机箱; 系统                                                                  |

## 其他产品详情

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



我们强大的品牌组合:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**