

# CPCI Serial R3.0 系统，带可插拔 PSU，4 U，9 插槽，带后 I/O

## 物料号

**24579-451**



4 U CompactPCI Serial R3.0 系统，带垂直卡槽，适用于 9 个 3 U 规格板卡和 1 个 3 U 可插拔电源。

## 功能

系统符合 IEC 60297 - 3 - 101、- 102、- 103；IEEE 1101.1、1101.10/11；背板符合 PICMG CPCI - S.0 R3.0

支持 PCIe Gen 4、10 Gbase-T、S-ATA 3 和 USB 3.2 Gen 2

以太网接口支持 10GBASE-KR 和 10GBASE-T 标准，并可实施 25GBASE-KR 标准

系统含垂直卡槽。适用 3U 规格板卡

9 槽背板，3U CompactPCI Serial（单星以太网拓扑），左侧系统插槽

通过 1 U 热插拔风扇单元散热

空气滤网结构支持定制

## 产品属性

产品类型: 系统

插槽数: 9

类型: 19" 机架安装

背板类型: 3 U CompactPCI Serial，以太网星型

数据传输: PCIe Gen4

每插槽的功率: 40W

交流输入电压: 100 – 240V

气流方向: 从下至上

机架高度: 4U

电源类型: (2) 可插拔 PSU

包含电源: 是

后部 I/O: 是

符合: PICMG CPCI-S.0 R3.0

深度: 275mm

高度: 177mm

机架宽度: 84HP

槽宽: 4HP

系统插槽: 左

## 其他产品详情

可直接下单采购标准品型号，也可应要求提供其他配置。

## 警告

### North America

All locations  
+1.763.422.2661  
Chat with us:  
nvent.com/schroff

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
nvent.com/schroff

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
nvent.com/schroff

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
nvent.com/schroff



我们强大的品牌组合:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**