

Varistar CP 接地编织带套件

物料号

24630-092



EMC/EMI 指令推荐，相比于电缆阻抗更小

符合 EAC 标准

符合 RoHS 标准

Compliant to ISO 6469-1 (Electrically propelled road vehicles - Part 1: Rechargeable energy storage system) - Section 6.2.2 Vibrations

功能

接地和连接编织带, 镀锡铜, 120 A 载流量

掌心集成, 无镀锡或压接线片, 提供出色的电气连接和高抗拉强度

抗振动和疲劳, 减少维护

减轻重量, 相较于同类带绝缘压接电缆, 能节省材料, 且降低阻抗

开箱即用, 无需切割, 剥线, 压接和穿孔

安装简单快速

EMC/EMI 指令推荐，相比于电缆阻抗更小

产品属性

包装数量: 1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE