


19 英寸温控器前面板，带数字显示屏，1 U，2.5 毫米，铝，RAL 7021

物料号

30118-360



19" 恒温器前面板，带数字显示屏，1 U

认证



功能

19 英寸前面板, 1 U, 恒温器开孔，带数字显示屏

产品属性

产品类型: 前面板

类型: 19" 前面板

附件类型: 前面板

安装: 正面螺钉安装

EMC 屏蔽: 否

材料: 铝

正面表面处理: 涂漆

反面表面处理: 涂漆

颜色代码: RAL 7021

机架高度: 1U

高度: 43mm

机架宽度: 95HP

宽度: 483mm

深度: 3mm

包装数量: 1

完成: 粉末涂层

Gross Weight: 0.109kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE