


水平横梁，前端，H-KD 型，重型，短喙，84 HP

物料号

34560-284



Combinations of horizontal rails and side panels

„+“ = can be combined, „-“ = combinations not recommended

Horizontal rail	Side panel	Horizontal rail	Side panel	Horizontal rail	Side panel
Horizontal rail	Side panel	Horizontal rail	Side panel	Horizontal rail	Side panel
Horizontal rail	Side panel	Horizontal rail	Side panel	Horizontal rail	Side panel
Horizontal rail	Side panel	Horizontal rail	Side panel	Horizontal rail	Side panel

H-KD 型（H-KD = 重型，短喙）铝挤出水平轨道，带阳极氧化表面和导电触点表面。印刷 HP 标记，用于对导轨进行快速定位。适用于 RatiopacPRO/-AIR 和 EuropacPRO/-rugged）。

认证



功能

安装在顶部和底部

短喙 (H-KD)

铝挤压件, 阳极氧化, 接触表面导电

产品属性

机架宽度: 84HP

包装数量: 1

完成: 阳极氧化

长度: 431.8mm

材料: 铝

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

产品类型: 水平横梁

类型: 重型, KD

搭配: 插箱; 仪器箱

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE