

# Guide Rail With Coding for CompactPCI/ VME64x, PC, 160 mm, 2 mm Groove Width, 灰色

## 物料号

**64568-090**



New generation of With Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

## 认证



## 功能

新一代编码型塑料导轨，实现 PCB 或模件盒的可靠固定

稳定性显著提高, 得益于优化设计和高质量材料 (PC)

提高防火安全性能, 符合 EN 45545-2 规范 R22, R23 和 R24 中的最高危险等级 HL3

“无卤素”, 符合 IEC 61249-2-21 标准

导轨可以卡入水平横梁（铝挤压件）或 1.5 mm 厚板中

可以通过螺栓固定到 H 型和 R 型水平横梁，以满足更高的抗冲击和振动要求

可选 ESD 夹，用于 PCB 和水平横梁之间的导电触点

存储温度：从 -40 °C.. 130 °C

产品属性

|                                                                                          |
|------------------------------------------------------------------------------------------|
| 材料: 纤维增强型塑料                                                                              |
| 颜色: 灰色                                                                                   |
| 包装数量: 1                                                                                  |
| 板深度: 160mm                                                                               |
| 槽宽: 2                                                                                    |
| 符合: EN 45545-2                                                                           |
| 产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac |
| 产品类型: 导轨                                                                                 |
| 类型: 编码                                                                                   |
| 搭配: 插箱; 仪器箱; 19" 机箱; 系统                                                                  |

其他产品详情

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

在立即与数生，可能会造成产品故障，引起火灾，甚至死亡。本文件为草案，所有信息仅供参考，不作为任何承诺或担保。

| North America     | Europe                 | Asia                 | Middle East & India         |
|-------------------|------------------------|----------------------|-----------------------------|
| All locations     | Straubenhardt, Germany | Shanghai, China      | Dubai, United Arab Emirates |
| +1.763.422.2661   | +49.7082.794.0         | +86.21.2412.6943     |                             |
| Chat with us:     | Betschdorf, France     | Qingdao, China       | +971.4.378.1700             |
| nvent.com/schroff | +33.3.88.90.64.90      | +86.532.8771.6101    | Bangalore, India            |
|                   | Warsaw, Poland         | Singapore            | +91.80.6715.2001            |
|                   | +48.22.209.98.35       | +65.6768.5800        | Istanbul, Turkey            |
|                   | Assago, Italy          | Shin-Yokohama, Japan | +90.216.250.7374            |
|                   | +39.02.932.7141        | +81.45.476.0271      | Chat with us:               |
|                   | Chat with us:          | Chat with us:        | nvent.com/schroff           |
|                   | nvent.com/schroff      | nvent.com/schroff    |                             |



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE