


熔断器支架，长型

物料号

69004-098



适用于玻璃熔断器插件 5 x 20 mm，符合 DIN 41 571标准，250 VAC，6.3 A。

认证



功能

适用于玻璃熔断器插件 5 x 20 mm至 DIN 41571, 250 VAC, 6.3 A

长型，适用安装面板1

触点镀银

产品属性

产品类型: 熔断器座

触点材料: 铜合金

材料: 聚对苯二甲酸丁二醇酯

其他产品详情

请考虑交货可能按标准包装数量规定执行（SPQ，如 5 件，10 件，50 件，等等）。可能会将不同的订购数量（例如 2 件）更改为下一个可能的交货数量（相当于标准包装数量）。

Required front panel drill hole: Ø 9 mm.

Dimensions of connecting pins: 0.7 × 0.6 mm.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE