

智能 PDU，EN1335，230VAC，1-PH，32 A

物料号

EN1335

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

功能

Enlogic EN1xxx 智能配电装置监控整个 PDU 的输入功率，提供计费级单元级别监控

高可视性的数据显示和交互式图形显示

测量冗余馈电的断路器负载，以避免意外停机

实现智能负载平衡，以提高电源效率和容量利用率

千兆以太网接口和冗余以太网 (10/100)

iPDU 直流电源冗余解决方案，最多可支持 64 个 PDU

无需安装工具的热插拔控制器

输入电压 230 VAC，1 相

C13，C19 个出口

产品属性

产品系列: Enlogic

类型: 智能 PDU

产品类型: 插排

插座类型: (32) C13; (6) C19

插座数量: 38

颜色: 黑色

断路器: 16 A，1 极，Hy-Mag

开关插座: 否

断路器数量: 2

输入电缆位置: 顶部供给

输入电压: 200 – 240V

相: 1 相

中断额定值: 5kAIC

最大输入功率: 7.44 kVA

电流（降额电流）: 32 A

输出电压: 200 – 240VAC

机架单元: 0U

插头类型: IEC 60309 332P6 (IP44)

计量类型: 输入

可拆卸输入电缆: 否

包装数量: 1

其他产品详情

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE