

280HTS 高散热锯齿形 Card-Lok

物料号

MA280HTS-4.30TM3L



280HTS

采用独特的锯齿形材设计，与同类尺寸的卡锁相比，可提供先进的热性能和夹持力，以实现高冲击和振动应用的卓越散热和保护。280HTS 可以逐渐替换大多数现有 280 系列 Card Lok 锁紧条 应用。应用：The Series 280HTS features sawtooth designed profiles along the length of the Card Lok that provide a continuous and uniform surface along the PCB/heat frame and along the cold wall for superior cooling performance

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

认证



功能

新锯齿型材设计，可实现卓越散热性能

型材 9.72 毫米 (0.365 英寸) x 9.65 毫米 (0.375 英寸)

重量 2.50 克/厘米 (0.022 盎司/英寸)

长度 71.12 毫米 (2.8 英寸) 至 325.12 毫米 (12.80 英寸)，12.7 毫米 (0.5 英寸) 增量

灵活的安装选项

平均夹持力：在 113 牛顿-厘米（10 英寸-磅）扭矩时，554 千克（1219 磅）

螺杆驱动

最大延展 11.68 毫米（0.460 英寸）

可提供黑色阳极氧化或化学镀镍表面处理

可用于冷板

产品属性

产品类型: PCB 固定器

材料: 铝

类型: 高热锯齿

热性能: 最佳

型材: 9.27 x 9.65 mm

夹持力: 272kgf

间隙宽度: PCB + (10.0 - 10.9 mm)

其他产品详情

nVent

可能会修改其产品技术参数以符合适用行业、军用或其他相关标准。除非另有书面协定，否则已取消或被取代的军用规格将被最新规格替代并完成认证。无论您是否已获得此类修改的通知，即使不同于原始技术参数或客户引用的技术参数，符合此类（最新或替代）技术参数的产品将被视为完全符合要求的合格产品。

应用：系列 280HTS 沿着 Card Lok 长度采用了锯齿设计的型材，可沿着 PCB/热框和冷壁提供连续均匀的表面，以实现卓越的冷却性能。

平均接头阻抗：取决于长度和应用。

Average Clamping Force: 554 kg (1219 lbs.) at 113 N-cm (10"-lbs).

Order Information: For customized products contact AskSchroff@nVent.com or 1-800-854-7086. Please provide drawing, quality clauses, and purchase order requirements.

Recomendet Gap width: PCB + 10.29 mm (0.405 in).

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE