

260 系列 PR Card-Lok

物料号

MTLCA260PR-3.80EHL



正向回缩技术可确保 Card-Lok

不会因剧烈振动或冲击导致的摩擦而卡在机箱中。联锁设计可确保在缩回驱动螺杆时，Card-Lok 与机箱插槽分离。

⚠警告：本产品可能使您接触包括铬（六价化合物）在内的化学物质，在加州已知铬会导致癌症和生殖健康问题。欲了解更多信息，请访问 www.P65Warnings.ca.gov。

功能

正向回缩 Card-Lok；适用于二级维护

5 段式，有轴设计

灵活的安装选项

提供金色化学氧化、本色化学氧化、黑色阳极氧化、黑色硬阳极氧化或无化学镀镍处理

可用于冷板

螺杆驱动

可提供扭矩限制选件；适用于二级维护

长度为 96.52 mm (3.80") 至 325.12 mm (12.80")，增量为 12.7 (0.5")

外形规格 6.35 mm (0.250") x 6.26 mm (0.270")

产品属性

产品类型: PCB 固定器

类型: 轴式

热性能: 最佳

型材: 6.35 x 6.26 mm

间隙宽度: PCB + (7.0 - 7.9 mm)

设计特征: 正向回缩

包装数量: 1

nVent

可能会不定期修改其产品技术参数以符合适用的工业、军用或其他相关标准。除非另有书面协定，否则已取消或被取代的军用规格将被最新规格替代并完成认证。无论您是否已获得此类修改的通知，即使不同于原始技术参数或客户引用的技术参数，符合此类（最新或替代）技术参数的产品将被视为完全符合要求的合格产品。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE