

EuropacPRO 19" Subrack Kit for DIN Connector, 滑轨, 可加装电磁屏蔽功能

适合DIN 连接器安装的非屏蔽式插箱 EN 60603-2, 插箱可装配在滑动导轨上以支持在机柜内的部署。



认证



功能

带 F 型（“灵活型”）侧板的插箱, 19" 支架, 带滑轨装配槽口

器件负载高达 11 千克

插箱可与滑轨搭配使用

水平轨道, 位于机箱后部, 适合连接器安装 (IEC 60603-2 / DIN 41612)

预装螺纹插件

技术参数

静态负载: 11kg

EMC 屏蔽: 否

产品类型: 插箱/机箱

Table 1/3

物料号	机架高度	深度	包装数量	用于安装	板深度	EMC 垫片类型
24553-192	3U	235mm	1	DIN 连接器	160mm, 220mm	不锈钢
24553-193	3U	295mm	1	DIN 连接器	160mm, 220mm, 280mm	不锈钢
24553-194	3U	355mm	1	DIN 连接器	160mm, 220mm, 280mm, 340mm	不锈钢
24553-492	6U	235mm	1	DIN 连接器	160mm, 220mm	不锈钢
24553-493	6U	295mm	1	DIN 连接器	160mm, 220mm, 280mm	不锈钢
24553-494	6U	355mm	1	DIN 连接器	160mm, 220mm, 280mm, 340mm	不锈钢

Table 2/3

物料号	包含手柄	安装	符合	完成	材料	机架宽度
24553-192	否	机架	IEC 60297-3-103	阳极氧化, 钝化	铝	84HP
24553-193	否	机架	IEC 60297-3-103	阳极氧化, 钝化		84HP
24553-194	否	机架	IEC 60297-3-103	阳极氧化, 钝化		84HP
24553-492	否	机架	IEC 60297-3-103	阳极氧化, 钝化		84HP
24553-493	否	机架	IEC 60297-3-103	阳极氧化, 钝化		84HP
24553-494	否	机架	IEC 60297-3-103	阳极氧化, 钝化		84HP

Table 3/3	
物料号	快速发货
24553-192	No
24553-193	No
24553-194	No
24553-492	No
24553-493	No
24553-494	No

其他产品详情

支持个性化配置: 支持较大范围高度，宽度和深度定制；根据不同应用可选多种规格导轨,内部附件和安装材料。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE