

# Interscale 19" 机架安装式机箱, 非网孔

灵活的 19" 机箱，带集成式 EMC 屏蔽部件。基于 nVent SCHROFF Interscale 平台，根据 IEC 60297-3-109 开发。



## 认证



## 功能

模块化桌面式机箱由 4 个易于装配的部件组成

根据 IEC 60297-3-109 标准开发（IEC 正在修订该标准）

集成 EMC 屏蔽

防护等级高达 IP 30

颜色 RAL 7016

可应要求提供改造或定制机箱

## 技术参数

|         |            |
|---------|------------|
| 材料:     | 钢; 铝       |
| 产品系列:   | Interscale |
| 产品类型:   | 小尺寸机箱      |
| 类型:     | 实心         |
| EMC 屏蔽: | 是          |

| Table 1/2 |      |          |      |         |    |                                  |
|-----------|------|----------|------|---------|----|----------------------------------|
| 物料号       | 机架高度 | 深度       | 包装数量 | 可用宽度    | 安装 | 符合                               |
| 14821-105 | 1U   | 221.45mm | 1    | 443.7mm | 机架 | IEC 60297-3-100, IEC 60297-3-109 |
| 14821-107 | 1U   | 310.35mm | 1    | 443.7mm | 机架 | IEC 60297-3-100, IEC 60297-3-109 |
| 14821-307 | 3U   | 310.35mm | 1    | 443.7mm | 机架 | IEC 60297-3-100, IEC 60297-3-109 |
| 14821-305 | 3U   | 221.45mm | 1    | 443.7mm | 机架 | IEC 60297-3-100, IEC 60297-3-109 |
| 14821-207 | 2U   | 310.35mm | 1    | 443.7mm | 机架 | IEC 60297-3-100, IEC 60297-3-109 |
| 14821-205 | 2U   | 221.45mm | 1    | 443.7mm | 机架 | IEC 60297-3-100, IEC 60297-3-109 |

| Table 2/2 |           |      |
|-----------|-----------|------|
| 物料号       | 完成        | 快速发货 |
| 14821-105 | 镀锌铝, 粉末涂层 | No   |
| 14821-107 | 镀锌铝, 粉末涂层 | No   |
| 14821-307 | 镀锌铝, 粉末涂层 | No   |
| 14821-305 | 镀锌铝, 粉末涂层 | No   |
| 14821-207 | 镀锌铝, 粉末涂层 | No   |
| 14821-205 | 镀锌铝, 粉末涂层 | No   |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE