

Interscale 桌面式机箱, 通风孔



灵活的桌面式机箱，带集成 EMC 保护装置和通风孔的侧板。基于 nVent SCHROFF Interscale 平台，根据 IEC 60297-3-109 开发。

认证



功能

模块化桌面式机箱由 4 个易于装配的部件组成

根据 IEC 60297-3-109 标准开发（IEC 正在修订该标准）

集成 EMC 屏蔽

防护等级高达 IP 20

颜色 RAL 7016

应要求提供改造或定制机箱

技术参数

材料:	铝; 钢
类型:	桌面式
产品系列:	Interscale
防护等级:	IP20
颜色代码:	RAL 7016
产品类型:	小尺寸机箱

Table 1/2						
物料号	高度	包装数量	宽度	深度	冷却	颜色
14825-154	43.7mm	1	221mm	177mm	穿孔	煤灰色
14825-254	88.1mm	1	221mm	177mm	穿孔	煤灰色
14825-155	43.7mm	1	221mm	221mm	穿孔	煤灰色
14825-175	43.7mm	1	310mm	221mm	穿孔	煤灰色
14825-195	43.7mm	1	399mm	221mm	穿孔	煤灰色
14825-197	43.7mm	1	399mm	310mm	穿孔	煤灰色
14825-255	88.1mm	1	221mm	221mm	穿孔	煤灰色
14825-275	88.1mm	1	310mm	221mm	穿孔	煤灰色
14825-295	88.1mm	1	399mm	221mm	穿孔	煤灰色
14825-297	88.1mm	1	399mm	310mm	穿孔	煤灰色
14825-375	132.6mm	1	310mm	221mm	穿孔	煤灰色
14825-395	132.6mm	1	399mm	221mm	穿孔	煤灰色
14825-397	132.6mm	1	399mm	310mm	穿孔	煤灰色

Table 2/2		
物料号	完成	快速发货
14825-154	镀锌铝, 粉末涂层	No
14825-254	镀锌铝, 粉末涂层	No

物料号	完成	快速发货
14825-155	镀锌铝, 粉末涂层	No
14825-175	镀锌铝, 粉末涂层	No
14825-195	镀锌铝, 粉末涂层	No
14825-197	镀锌铝, 粉末涂层	No
14825-255	镀锌铝, 粉末涂层	No
14825-275	镀锌铝, 粉末涂层	No
14825-295	镀锌铝, 粉末涂层	No
14825-297	镀锌铝, 粉末涂层	No
14825-375	镀锌铝, 粉末涂层	No
14825-395	镀锌铝, 粉末涂层	No
14825-397	镀锌铝, 粉末涂层	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE