

MTCA 导轨

适用 MicroTCA.0、MicroTCA.1 和 MicroTCA.4 的导轨。



认证



功能

导轨，适用 MicroTCA.0, MicroTCA.1 和 MicroTCA.4

无需工具即可轻松安装在 1 HP 间距的网格中；两个导轨之间的最小间距为 3 HP（Compact Size）

技术参数

Table 1/1						
物料号	类型	搭配	材料	颜色	包装数量	快速发货
20849-194	MicroTCA AdvancedMC	MicroTCA 系统	聚对苯二甲酸丁二醇酯	红色	10	No
20849-196	MicroTCA 电源	MicroTCA 系统	聚对苯二甲酸丁二醇酯	黄色	10	No
20849-198	MicroTCA 托架集线器	MicroTCA 系统	聚对苯二甲酸丁二醇酯	灰色	10	No
20849-200	MicroTCA 通用型	MicroTCA 系统	聚对苯二甲酸丁二醇酯	绿色	10	No

物料号	类型	搭配	材料	颜色	包装数量	快速发货
20849-202	MicroTCA 托架集线器	MicroTCA 系统	聚对苯二甲酸丁 二醇酯	灰色	10	No
20849-195	MicroTCA AdvancedMC	MicroTCA 系统	聚对苯二甲酸丁 二醇酯	红色	100	No
20849-201	MicroTCA 通用型	MicroTCA 系统	聚对苯二甲酸丁 二醇酯	绿色	100	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE