


用于绝缘背板的欧标板卡安装套件



使用基于 IEC 60297

标准的安装套件，可将欧卡规格电路板和双宽欧卡规格电路板水平安装在 19" 机架中。

认证



功能

使用内部安装套件，欧卡单板和双宽欧卡单板可以水平安装在 19" 机箱中 (IEC 60297)

交付范围足以安装一个 3 U 板（欧卡规格）或一个 6 U 板（双宽欧卡规格）

技术参数

材料: 铝
搭配: 机箱
产品类型: 安装套件
产品系列: MultipacPRO

Table 1/1

物料号	机架高度	包装数量	快速发货
20860-116	1U	1	No

物料号	机架高度	包装数量	快速发货
20860-118	2U	1	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE