


Novastar 滑轨, 短款, 15 公斤



Novastar L型滑动导轨，承载能力 15kg，用于安装在机柜立柱或 19" 面板/角轨安装件上。

认证



功能

静态承载能力 15 千克/每对

碳钢, 1.5 mm, 覆铝锌表面

适用于在机构立柱或 19" 面板/角轨安装件上安装

以 1 U 增量调节

技术参数

静态负载: 15kg

产品类型: 滑轨

材料: 钢

Table 1/1

物料号	完成	长度	包装数量	快速发货
27230-184	镀锌铝	55mm	2	No

物料号	完成	长度	包装数量	快速发货
27230-185	镀锌铝	55mm	10	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations +1.763.422.2661 Chat with us: nvent.com/schroff	Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff	Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff	Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE