

带梯形把手的插件套件, 非屏蔽型, 灰色



面板，带静态把手和平板式前面板。灰色把手装配在前面板上。

认证



功能

平板式前面板

不带助拔功能的把手

技术参数

材料: 铝
完成: 阳极氧化; 钝化
产品类型: 前面板
类型: 带把手的前面板 (PIU)

Table 1/3

物料号	机架高度	机架宽度	包装数量	手柄类型	安装	正面表面处理
20818-017	3U	3HP	1	梯形, 静态	正面螺钉安装	阳极氧化

物料号	机架高度	机架宽度	包装数量	手柄类型	安装	正面表面处理
20818-018	3U	4HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-019	3U	5HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-020	3U	6HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-021	3U	7HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-022	3U	8HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-023	3U	10HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-024	3U	12HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-025	6U	4HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-026	6U	5HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-027	6U	6HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-028	6U	8HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-029	6U	10HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-120	6U	12HP	1	梯形，静态	正面螺钉安装	阳极氧化
20818-162	6U	7HP	1	梯形，静态	正面螺钉安装	阳极氧化

Table 2/3						
物料号	反面表面处理	边缘处理	可燃性等级	符合	EMC 屏蔽	高度 (H)
20818-017	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm

物料号	反面表面处理	边缘处理	可燃性等级	符合	EMC 屏蔽	高度 (H)
20818-018	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm
20818-019	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm
20818-020	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm
20818-021	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm
20818-022	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm
20818-023	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm
20818-024	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	128.4mm
20818-025	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	261.8mm
20818-026	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	261.8mm

物料号	反面表面处理	边缘处理	可燃性等级	符合	EMC 屏蔽	高度 (H)
20818-027	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	261.8mm
20818-028	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	261.8mm
20818-029	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	261.8mm
20818-120	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	261.8mm
20818-162	钝化	否	UL® 94V-0	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	否	261.8mm

Table 3/3		
物料号	宽度 (W)	快速发货
20818-017	14.9mm	No
20818-018	20mm	No
20818-019	25mm	No
20818-020	30.1mm	No
20818-021	35.2mm	No
20818-022	40.3mm	No

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE