

PMC 夹层卡前面板, 未处理, 带 EMC 屏蔽



夹层前面板安装在 PMC

前面板开孔中。提供不同处理方式的版本。适用于 O 形环 EMC 垫片。

认证



功能

夹层前面板安装在带 PMC 开孔的前面板中

EMC 屏蔽, 带导电 O 型圈

技术参数

产品类型: 前面板
类型: 不带把手的前面板
EMC 屏蔽: 是

Table 1/3

物料号	包装数量	附件类型	安装	EMC 垫片类型	正面表面处理	反面表面处理
20835-598	1	前面板	正面螺钉安装	O 形环	阳极氧化	导电
20835-889	1	前面板	正面螺钉安装	O 形环	阳极氧化	导电

物料号	包装数量	附件类型	安装	EMC 垫片类型	正面表面处理	反面表面处理
20835-890	1		正面螺钉安装			
20835-922	1		正面螺钉安装		镀铬	镀铬
20835-923	1		正面螺钉安装		镀铬	镀铬
20835-893	10		正面螺钉安装		镀铬	镀铬
20835-924	10		正面螺钉安装		镀铬	镀铬
20835-928	10		正面螺钉安装		阳极氧化	导电

Table 2/3						
物料号	边缘处理	符合	深度	完成	高度	材料
20835-598	否	PMC 夹层板, IEEE P1386	2.5mm	阳极氧化	74mm	铝
20835-889	否	PMC 夹层板, IEEE P1386	2.5mm	阳极氧化	74mm	铝
20835-890	否	PMC 夹层板, IEEE P1386			74mm	锌
20835-922	是	PMC 夹层板, IEEE P1386			74mm	锌
20835-923	是	PMC 夹层板, IEEE P1386			74mm	锌
20835-893	是	PMC 夹层板, IEEE P1386			74mm	锌
20835-924	是	PMC 夹层板, IEEE P1386			74mm	锌

物料号	边缘处理	符合	深度	完成	高度	材料
20835-928	否	PMC 夹层板, IEEE P1386			74mm	锌

Table 3/3		
物料号	宽度	快速发货
20835-598	12.7mm	No
20835-889	12.7mm	No
20835-890	12.7mm	No
20835-922	12.7mm	No
20835-923	12.7mm	No
20835-893	12.7mm	No
20835-924	12.7mm	No
20835-928	12.7mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE