

电源,19", 交流/直流线性稳压器, 单柜

线性稳压器, 适用需要极低输出噪音水平的应用。



认证



功能

1 输出电压

控制精度高, 残余纹波低且干扰低

230 VAC 电源/线路电压 (可通过电源/线路电压转换套件转换为 115 VAC 电压输入)

适用医疗应用 (8 mm安全间隙)

技术参数

Table 1/2

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13105-004	19" 线性稳压器	230V	16W	1	24V	0.6A
13105-001	19" 线性稳压器	230V	8W	1	5V	1.5A
13105-002	19" 线性稳压器	230V	13W	1	12V	1.1A

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13105-003	19" 线性稳压器	230V	15W	1	15V	1A
13105-006	19" 线性稳压器	230V	20W	1	5V	4A
13105-007	19" 线性稳压器	230V	31W	1	12V	2.8A
13105-008	19" 线性稳压器	230V	33W	1	15V	2.2A
13105-009	19" 线性稳压器	230V	36W	1	24V	1.5A
13105-011	19" 线性稳压器	230V	30W	1	5V	6A
13105-012	19" 线性稳压器	230V	50W	1	12V	4.2A
13105-013	19" 线性稳压器	230V	53W	1	15V	3.5A
13105-014	19" 线性稳压器	230V	60W	1	24V	2.5A

Table 2/2						
物料号	机架高度	机架宽度	深度	包装数量	认证	快速发货
13105-004	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS	No
13105-001	3U	6HP	171.93mm	1	RoHS, CE, EN 62368-1	No
13105-002	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS	No
13105-003	3U	6HP	171.93mm	1	RoHS, CE, EN 62368-1	No
13105-006	3U	10HP	171.93mm	1	RoHS, CE	No
13105-007	3U	10HP	171.93mm	1	CE, RoHS	No

物料号	机架高度	机架宽度	深度	包装数量	认证	快速发货
13105-008	3U	10HP	171.93mm	1	RoHS, CE	No
13105-009	3U	10HP	171.93mm	1	CE, RoHS	No
13105-011	3U	14HP	171.93mm	1	RoHS, CE	No
13105-012	3U	14HP	171.93mm	1	CE, RoHS	No
13105-013	3U	14HP	171.93mm	1	RoHS, CE	No
13105-014	3U	14HP	171.93mm	1	CE, RoHS	No

其他产品详情

请单独订购前面板。

输出数据是在Ta = 0 ... 50 °C 环境下测得。

警告

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE