

电源, 19", 交流/直流线性稳压器, 三路输出

线性稳压器, 适用需要极低输出噪音水平的应用。



认证



功能

3 种输出电压, 电气隔离

控制精度高, 残余纹波低且干扰极低

230 VAC 电源/线路电压 (可通过电源/线路电压转换套件转换为 115 VAC)

适用医疗应用 (8 mm安全间隙)

技术参数

Table 1/3

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13105-051	19" 线性稳压器	230V	8W	3	5V	0.5A
13105-052	19" 线性稳压器	230V	20W	3	5V	1.5A
13105-053	19" 线性稳压器	230V	39W	3	5V	3A

Table 2/3						
物料号	电压 2	电流 2	电压 3	电流 3	机架高度	机架宽度
13105-051	12V	0.2A	12V	0.2A	3U	6HP
13105-052	12V	0.5A	12V	0.5A	3U	10HP
13105-053	12V	1A	12V	1A	3U	14HP

Table 3/3				
物料号	深度	包装数量	认证	快速发货
13105-051	171.93mm	1	RoHS, CE, EN 62368-1	No
13105-052	171.93mm	1	CE, RoHS	No
13105-053	171.93mm	1	RoHS, CE	No

其他产品详情

请单独订购前面板。

输出数据是在Ta = 0 ... 50 °C 环境下测得。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE