

PSU 19" 交流/直流最大功率 100 W, 三路输出



Pluggable 19" Power Supplies with H15 connector for fanless applications. 具有广泛的交流输入范围和三种输出电压。

认证



功能

宽幅输入电压 90 ... 254 VAC 和 100 ... 360 VDC, 带有源功率因数校正 (PFC)

3 种输出电压

电源信号: 输出电压正常

高功率密度

技术参数

Table 1/3

物料号	类型	交流输入电压	电源	输出电压数	电压 1	电流 1
13100-122	19" 开关模式	90 - 264V	100W	3	5V	8A
13100-123	19" 开关模式	90 - 264V	100W	3	5V	8A

Table 2/3						
物料号	电压 2	电流 2	电压 3	电流 3	机架高度	机架宽度
13100-122	12V	2.5A	12V	2.5A	3U	8HP
13100-123	15V	2A	15V	2A	3U	8HP

Table 3/3			
物料号	深度	包装数量	快速发货
13100-122	171.93mm	1	No
13100-123	171.93mm	1	No

其他产品详情

请单独订购前面板。

电源电压 > 190 VAC 且 Ta = -25 ... 50 °C 时的输出数据。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	Emirates
Chat with us:	Betschdorf, France	Qingdao, China	+971.4.378.1700
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	Bangalore, India
	Warsaw, Poland	Singapore	+91.80.6715.2001
	+48.22.209.98.35	+65.6768.5800	Istanbul, Turkey
	Assago, Italy	Shin-Yokohama, Japan	+90.216.250.7374
	+39.02.932.7141	+81.45.476.0271	Chat with us:
	Chat with us:	Chat with us:	nvent.com/schroff
	nvent.com/schroff	nvent.com/schroff	



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE