

PSU 19" DC/DC Coolpower 100 W, 单柜

带 H15 连接器的可插拔 19" 电源，适用无风扇应用。



认证



功能

宽幅电压输入：20 至 72 VDC

主电路和次级电路之间有电气隔离

高功率密度

带外部开/关

技术参数

Table 1/2

物料号	类型	直流输入电压	电源	输出电压数	电压 1	电流 1
13103-003	19" 直流/直流转换器	20 – 72V	102W	1	12V	8.5A
13103-004	19" 直流/直流转换器	20 – 72V	100W	1	15V	6.7A

物料号	类型	直流输入电压	电源	输出电压数	电压 1	电流 1
13103-002	19" 直流/直流转换器	20 – 72V	100W	1	5V	20A

Table 2/2					
物料号	机架高度	机架宽度	深度	包装数量	快速发货
13103-003	3U	6HP	171.93mm	1	No
13103-004	3U	6HP	171.93mm	1	No
13103-002	3U	6HP	171.93mm	1	No

其他产品详情

请单独订购前面板。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE