


RatiopacPRO空气密封



自粘式密封件可以封闭后水平横梁和底板之间的空间，以免空气进入 RatiopacPRO Air 机箱。

认证



功能

风道密封条可以封闭后水平横梁和底板之间的空间。

自粘式密封件可粘在底板上

技术参数

产品类型: 导风
 搭配: 仪器箱
 材料: 聚乙烯
 产品系列: RatiopacPRO AIR

Table 1/1

物料号	机架宽度	包装数量	长度	快速发货
20833-351	42HP	1	218.4mm	No
20833-352	63HP	1	325.1mm	No

物料号	机架宽度	包装数量	长度	快速发货
20833-353	84HP	1	431.8mm	No

其他产品详情

如需带风扇或离心风扇托盘的后面板，请查看 RatiopacPRO 附件目录。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE