

插座条，带 2 根供电电缆, 3 相

模块化、紧凑型 PDU，带两个电源线输入端，可连接至 A 和 B 进给电源。单个机箱设计，节省空间。



认证



功能

可以提供水平和垂直装配

两根连接器电缆（沿长度方向减半），3 m（带开口端），2 x 3 相，400 VAC（红色、黑色、白色区域）

安装期间，插座条可以全方位旋转（90° 增量）

安装高度 1 U

带 IEC 60320-C13 插座和 SCHUKO 插座的电源分配单元

技术参数

长度:	1848.5mm
材料:	铝; 聚酰胺
颜色:	灰色; 黑色; 红色
产品类型:	插排

Table 1/2

物料号	插座类型	插座数量	开关插座	交流电压	包装数量	深度
-----	------	------	------	------	------	----

60110-286	IEC C13, SCHUKO	36	否	400V	1	44mm
60110-287	IEC C13	48	否	400V	1	44mm

Table 2/2			
物料号	完成	高度	快速发货
60110-286	阳极氧化	44mm	No
60110-287	阳极氧化	44mm	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE