

插排, SCHUKO, 带 Wieland® 输入



模块化、紧凑型 PDU，支持多种功能。PDU 采用 1 U x 1 U 铝机箱，可轻松集成在机架中。Wieland 连接器允许不同输入线轻松连接

认证



功能

安装高度 1 U

通过 SCHUKO 插座输出

通过 Wieland® GST 18 插头输入

安装时，插排可以向四个方向旋转（90°增量）

水平或垂直安装

符合 DIN 57620 标准

技术参数

长度: 438.5mm

材料: 铝; 聚酰胺

产品类型: 插排

Table 1/2

物料号	插座类型	插座数量	开关插座	交流电压	功能	包装数量
-----	------	------	------	------	----	------

60110-345	SCHUKO	8	否	230V		1
60110-344	SCHUKO	8	否	230V		1
60110-343	SCHUKO	8	否	230V		1
60110-352	SCHUKO	6	否	230V	过流保护	1
60110-354	SCHUKO	6	否	230V	过流保护	1
60110-353	SCHUKO	6	否	230V	过流保护	1

Table 2/2				
物料号	颜色	深度	完成	快速发货
60110-345	红色	44mm	阳极氧化	No
60110-344	黑色	44mm	阳极氧化	No
60110-343	灰色	44mm	阳极氧化	No
60110-352	灰色	44mm	阳极氧化	No
60110-354	红色	44mm	阳极氧化	No
60110-353	黑色	44mm	阳极氧化	No

其他产品详情

请单独订购垂直安装支架。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE