

通用伸缩滑轨, 轻型, 2 U

轻型通用型伸缩滑轨, 2 U。



认证



功能

轨道宽度 $k = 9.7 \text{ mm}$, 延长部件/抽屉最大安装宽度 $w = 429 \text{ mm}$

在 19" 支柱上横向安装 (不占用 19" 平面即可安装延长部件/抽屉)

全延长状态下可锁定

静态承载能力每对 46 - 57 千克

延长宽度 > 110 %

技术参数

材料: 钢

产品类型: 伸缩滑轨

完成: 镀锌

Table 1/1

物料号	长度	包装数量	静态负载	类型	快速发货
-----	----	------	------	----	------

20110-071	356mm	2	57kg	通用型	No
20110-077	610mm	2	46kg	通用型	No
20110-076	584mm	2	46kg	通用型	No
20110-075	559mm	2	46kg	通用型	No
20110-074	508mm	2	55kg	通用型	No
20110-072	406mm	2	55kg	通用型	No
20110-073	457mm	2	55kg	通用型	No

其他产品详情

在非标准应用中，无需附加组件也可安装通用伸缩滑轨，除 19" 机柜外也是如此。

要在 19" 面板上安装，请单独订购装配套件。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE